

R300 Series Indicators Manual Update

The Reference Manual for Rinstrum's R300 Series of indicators has been updated to the newest firmware versions. Changes to the manual include the following:

- Added menu item to enable/disable buzzer
- Added menu item to display oz weights as lb:oz (K35x)
- Added new print tokens for unit switching
- Added setpoint alarms (K356)
- Added QA timeout settings to CLOC menu

The reference manual is downloadable the pages of the following products:

- [R320 ABS Indicators](#)
- [R323 Stainless-Steel Indicators](#)
- [R323 Classic Stainless-Steel Indicators](#)
- [R323 Stainless Steel Panel Mount Indicators](#)

The manual is also downloadable from the following direct link:

[R300 Reference Manual](#)



Rinstrum Sponsors Weighing at Bridgestone World Solar Car Challenge

Rinstrum was once again the weighing sponsors for the World Solar Car Challenge, the 3000km race involving solar-powered vehicles that is held on a bi-annual basis.

Our Solar Car Scale was used by the scrutineering team, and consisted of four 75kg planar beam loadcells to provide 300% overload-protected 200kg scales that can be deployed on any flat surface, including carpet. Overall, the technology allowed for low-profile rugged scales that are ideal for a wide variety of medical and industrial applications.

Rinstrum updated the Lua scripting in the R423 unit that is mounted in the carry case along with a printer.

More information on Rinstrum's Involvement in this unique challenge can be read in the [original news article](#), which also includes a selection of photographs of the event.



C500 Series Reference Manual Updated

The reference manual for the C500 indicator has been updated with a few changes done to be in line with changes done to the C500-500 application software.

This manual can be downloaded from the [C500 Product Page](#).



X300 Series Reference Manual Updated

The reference manual for the X300 Series of Indicators has been updated. The following changes have been done:

- Added menu item to enable/disable buzzer
- Added menu item to display oz weights as lb:oz
- Added new print tokens for unit switching and amended print token \95 to indicate that it decrements to 3 with wrapping
- Fixed reported bugs and edited for clarity, style, and grammar.



The updated manual is downloadable from the [X320 product page](#).

Australian Trade Approval for Zemic H8C and B8D Load Cells

The National Measurement Institute has approved Zemic H8C and B8D Load Cells for trade in Australia. The B8D-C3-200kg-6B Load Cell received certificate no. NMI S751 and the H8C-C3-100kg-4B Load Cell received certificate no. NMI S752.



AUSTRALIA
Rinstrum Pty Ltd

Ph: + 61 7 3216 7166
Email: sales@rinstrum.com

USA
Rinstrum Inc

Toll Free +1 877 829 9152
Ph: +1 248 680 0320
Email:
sales.usa@rinstrum.com

EUROPE
Rinstrum Europe GmbH

Ph: +49(0)2173 165 62- 10
Email: sales.eu@rinstrum.com

www.rinstrum.com